

Product Data Sheet „motion sprint 900 SL med“

name of machine:	motion sprint 900 SL med
manufacturer:	Sprintex Trainingsgeräte GmbH
part number:	F-MED-ML-900
monitor:	7" TFT – capacitive touch display, high resolution coloured display, including speaker for acoustical feedback optional: inductive Qi charging module for mobile devices
power range:	0,1-17 km/h adjustable in 0.1 km/h steps with performance package: 0,1-22 km/h, optional: running direction reversal up to 5km/h
inclination angle:	0-15%, optional: -3 to 12%
drive:	energy-saving, brushless 1100 W DC motor
applied standards:	DIN EN ISO 20957-1 S-A-I, DIN EN 60601-1-2, DIN 957-6 S-A-I, DIN EN 60601 1-2 230V/50- 60 Hz, EWG, separate fuse protection necessary
classification:	EU 2017/745 Art. 120; class IIa
usage class:	S, I following DIN EN ISO 20957-1
accuracy class:	A (high accuracy) following DIN EN ISO 20957-1
ambient conditions:	humidity <80%; ambient temperature 0-45°C
parameters displayed:	programme name, time, pulse, watt (in 1 watt-steps), km/h (0,1 km/h steps), rpm, L/R (motion balance system indicator, 00:00), HRV, km (in meter1-100, then 10 m-steps 1,00-99,99), k-cal, Level
pulse measurement:	standard: Polar®-Auto connection system (Bluetooth® Low Energy & 5kHz), interference free with automatic connection and disconnection, downward compatible optional: ANT+ Standard for compatibility to Garmin sensors and Polar® Verity Sense
interfaces:	optional: Bluetooth®, NFC, RFID
programmes:	standard: Quick, Time, Pulse (incline or speed controlled) optional: Watt sensitive, Therapy, Interval, K-Cal, Hills, Distance
equipment:	stable railing, low-maintenance, energy-saving slat technology, optional: underarm supports, bar railing, safety arch for personal safety and many more
maximum user weight:	160 kg/ 352 lbs
measurements:	173 x 76 x 145 cm/69 x 30 x 58" (LxWxH) running surface 155 x 50 cm/61 x 19" ascent height 28 cm/11"
net weight:	177 kg/391 lbs
gross weight:	depending on package mode chosen (land, sea, air)



Weight and dimensions may differ depending on accessories.

Frame colour depending on individual specifications.

Technical changes reserved.

Warning: Only authorized service staff is allowed to open the unit.

If you need further information, please refer to user manual or contact us at: +49-6305-71499-0.

(Issued: June 2024)